

176x176x89 mm

SUNON



Alveolate Motor

315-335CFM



Model	P/N	Bearing	Rating Voltage	Freq.	Power Current	Power Consumption	Speed	Air Flow	Static Pressure	Noise	Weight
		● VAPO ○ BALL ◎ Sleeve	(VAC)	(Hz)	(AMP)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
A1179-HBT	TC.GN	○	115	50/60	0,25/0,27	24/30	2800/3250	315/335	0,65/0,8	62/66	1960
A1179-HBL	TC.GN	○	115	50/60	0,25/0,27	24/30	2800/3250	315/335	0,65/0,8	62/66	1960
A2179-HBT	TC.GN	○	220-240	50/60	0,11/0,15	23/30	2800/3250	315/335	0,65/0,8	62/66	1960
A2179-HBL	TC.GN	○	220-240	50/60	0,11/0,15	23/30	2800/3250	315/335	0,65/0,8	62/66	1960

Frame : Aluminum alloy



*All model could be customized on voltage or any other requirements to fit your need.

*Specifications subject to change without notice. Please Visit SUNON web site at <http://www.sunon.com> for update information.