

A

B

C

D

E

F

G

H

1


2

3

4

5

6



Operating Temperature: 75°C max.

Material
Terminal : Copper
Insulation : PVC
Plating : TIN

Best.-Nr.	WIRE RANGE mm ² / AWG	TAB (mm)	T (mm)	DIMENSION					COLOR
				B (mm)	dø (mm)	Dø (mm)	L (mm)	H (mm)	
74 50 98	0.5~1.5mm ² 22~16 AWG	2.8 x 0.5	0.3	4	3.7	5.2	18.5	10	RED
74 51 10		2.8 x 0.8	0.3	4	3.8	6	20		
74 51 22		4.8 x 0.5	0.35	5.7	3.6	5	18.5		
74 51 36		4.8 x 0.8	0.35	5.6	3.4	5	19		
74 51 51		6.4 x 0.8	0.35	7.6	3.5	5.3	21		
74 51 66	1.5~2.5mm ² 16~14 AWG	4.8 x 0.5	0.35	5.6	4.1	5.66	19	10.5	BLUE
74 51 80		4.8 x 0.8	0.35	5.6	4.2	5.8	19		
74 51 94		6.4 x 0.8	0.4	7.5	4.2	5.66	21		
74 52 08	4~6mm ² 12~10 AWG	6.4 x 0.8	0.4	7.6	5.4	7	24	13	YELLOW

Female Dis connector Series