

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0026640100
Status: Obsolete
Description: 3.96mm (.156") Pitch Header, Vertical, Press-fit Plastic Peg, with Round Pin, 10 Circuits, Tin (Sn) Plating

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	42441
Application	Power, Wire-to-Board
Product Name	N/A

Physical


Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	None
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.56mm (.140")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	3.96mm (.156")
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	0°C to +75°C

Electrical

Current - Maximum per Contact	7A
Voltage - Maximum	250V

Material Info

Old Part Number	42441-0010
-----------------	------------



Series
image - Reference only

EU RoHS **China RoHS**

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

42441Series

Mates With

3069 , 2139 , 2145 , 6442 , 7674 , 7675 , 41695 , L ink:41815

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION