

TY-type Twin Wheel Caster






Characteristic

Small and light weight caster with excellent driving stability and turning ability.
Having original appearance, it suits for any kind of interior device. New stopper is applied to obtain better operability.



Application

Medical instruments /
Office automation appliances /
Audio racks / TV tables /
Various types of wagons, etc.

TY40N□S / TY50N□S (with stopper)



TY40S / TY50S (with stopper)



Specification

Model No.	Material		Allowable Load (kg)	Code No.
	Body	Wheel		
TY40	PA	PA	40	19011
TY40S				19021
TY40N2.5				19012
TY40N2.5S				19022
TY40N3				19013
TY40N3S				19023
TY40N8				19014
TY40N8S				19024
TY40N10				19015
TY40N10S				19025
TY50	PA	PA	60	19016
TY50S				19026
TY50N3				19017
TY50N3S				19027
TY50N8				19018
TY50N8S				19028
TY50N10				19019
TY50N10S				19029
TY50N12				19020
TY50N12S				19030

Size List

Model No.	A	B	C	D	E	G	d	H1	H2	J1	J2	K	L	W1	W2	
TY40		φ28	φ39	φ40	15	φ5		49		t2.6				44	20	
TY40S	42															
TY40N2.5																
TY40N2.5S	42															
TY40N3																
TY40N3S	42															
TY40N8																
TY40N8S	42															
TY40N10																
TY40N10S	42					M10×1.5						14	12			
TY50		φ40	φ54	φ50	17	φ5.5		65		t3				49	21	
TY50S	49															
TY50N3																
TY50N3S	49															
TY50N8																
TY50N8S	49															
TY50N10																
TY50N10S	49															
TY50N12																
TY50N12S	49					M12×1.75						17	14			

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.