



Thermometer strips

testoterm thermometer strips are self-adhesive foils with temperature sensitive elements for temperature control and regulation. Used, for example, for measurements on moving parts, for long-term monitoring and on small parts.

+37 to +65 °C

Part no. 0646 0108

+71 to +110 °C

Part no. 0646 0916

+116 to +154 °C

Part no. 0646 1724

+161 to +204 °C

Part no. 0646 2532

+204 to +260 °C

Part no. 0646 3341

+249 to +280 °C

Part no. 0646 0005

Self-adhesive

- Irreversible change in second
- Practical booklets and strips
- Thermometer strips e.g. for labelling

Technical data

Accuracy: From +43°
+160°C: $\pm 1\% \pm 1^\circ\text{C}$ of
reading

Max. operating temperature
respective measuring range

Storage of clock indicator
months; other measuring
max. storage temperature
refrigerator is recommended

l x w: 50 x 18 mm or 100 x 18 mm