

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 254714

3266 cermet trimmer potentiometer

Electrical characteristics:

Standard resistance range: 10(Ohms) - 2M(Ohms)

Resistance tolerance: $\pm 5\%$, $\pm 10\%$ Terminal resistance: $\leq 1\%R$ or 2(Ohms)Contact resistance variation: $\leq 3\%R$ or 3(Ohms)

Environment characteristics:

Rated power: $+70^{\circ}$ 0.25W, $+125^{\circ}$ 0WTemperature range: -55° $+125^{\circ}$

Physical characteristics:

Total mechanical travel: 14 ± 2 cyclesStarting torque: ≤ 25 mN.mClutch torque: ≤ 25 mN.m

Standard packaging: 50 pcs/tube

Model	Resistance(Ω)
3266W-1-103	10,000
3266W-1-104	100,000
3266W-1-105	1,000,000
3266W-1-201	200
3266W-1-202	2,000
3266W-1-203	20,000
3266W-1-204	200,000
3266W-1-253	25,000
3266W-1-500	50
3266W-1-501	500
3266W-1-502	5,000
3266W-1-503	5,000
3266W-1-504	500,000

