

A durable three pin, fused panel plug, with 0.8mm solder lug / spade terminals. Can be mounted above the panel on any thickness of material or below the panel for up to 2.5mm thick material. Suitable for use on measuring instruments, SWPS, ITE and OA.

For panel cut-out, use punch number 074-0040 (pull through) or 024-0010 (punch and die).

Weight approximately 10g.

Approvals TUV and NETA/C

MATERIAL

HOUSING : Nylon 66, black
UL 94 V0

CONTACTS : Brass, nickel plate

ELECTRICAL

Current Rating : 10 Amps

Voltage Rating : 250 Vac


Insulation : 1000 MΩ @ 500 Vac

Resistance


Withstanding Voltage : 2000 Vac for 1 minute
between line to gnd.

Temperature Range : -20°C to +80°C

Dimensions



CONVERTED FROM PS0901 ISS2 (22.06.98) IN JAN 2003

DrgNo 522-0010			TITLE FUSED MAINS CONNECTOR – PANEL PLUG					ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES		 			
		ISSUE 3	GENERAL SPECIFICATION FOR 522-0010	CUSTOMER			FILTER REF						
				Aprvd Date	19.02.08	Aprvd By	MC	Drwn by	BS	Scale:	NTS	Sheet	1/ 1
				© DEM Manufacturing Limited E-Mail sales@dem.com, Website www.dem-uk.com. Phone +44 1724 273200 Fax +44 1724 280353									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Deltron:](#)

[522-0010](#)