


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT* PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MAX. PANEL THICKNESS	MIN. LOOP TENSILE	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)												
PLP1S	.06 (1.5)	1.00 (25.4)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	5.3 (135)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.24 (109)
PLP1.5S	.06 (1.5)	1.50 (38.1)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	6.7 (170)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.29 (132)
PLP2S	.06 (1.5)	1.75 (44.5)	.050 (1.3)	.190 (4.8)	.300 (7.6)	.354 (9.0)	.370 (9.4)	7.88 (200)	.330 (8.4)	.250 (6.4)	.125 (3.2)	50 (222)	STANDARD	.32 (145)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL, PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

2) SEE DRAWING SS-26888(A) FOR PLP1.5I.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

								TITLE						
								STRAP, PUSH MOUNT-PLP						
								CUSTOMER DRAWING						
								ITEM REVISION NAME				SS-26803/AB		
								DATASET FILE NAME				SS-26803_DC/AB SS-26803_REV07		
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:		
								.x ± .1 [2.5] .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES ± - - - -				NYLON 6.6		
												THIRD ANGLE PROJECTION		DRAWING NUMBER:
												SS-26803		
07	11/04/14	BWG	MPH	JADE	CHANGED "B" DIMENSION TO .190 AND UPDATED TITLE BORDER AND NOTES. SEE ECN FOR COMPLETE DETAILS.		SS-26803/07							
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE
								RAM	4/27/93	HVP	NONE			A