

Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to NEMA 5-20P), 10-ft.

MODEL NUMBER: **P049-010**



Description

Tripp Lite Heavy-Duty C19 to 5-20P 10 ft. Power Cable. Constructed with 3 x 12 AWG copper conductors, fully molded ends, 125V/20A rating.

Features

- Molded, Heavy-Duty Power Cable, 10 ft.
- IEC-60320-C19 to NEMA 5-20P
- 12 AWG x 3C, SJT, 20A, 125 Volt
- RoHS Compliant

Specifications

INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.1
PHYSICAL	
Shipping Dimensions (hwd / in.)	12.8 x 8.9 x 0.1
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 0.25
Shipping Weight (lbs.)	1.7
Shipping Weight (kg)	0.77
Color	Black

Highlights

- C19 to 5-20P Power Cable, 10 ft.
- 12 AWG x 3C
- RoHS Compliant

Package Includes

- C19 to 5-20P Power Cable, 10 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	NEMA 5-20P
Side B - Connector 1	IEC-320-C19
CERTIFICATIONS	
Approvals	UL-approved
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>