





NOTES:

- HIROSE COMPATIBLE
- 100% ELECTRICAL TESTING FOR:
CONTINUITY AND SHORTS. HI-POT AT 150 VDC FOR 100ms
FREQUENCY RANGE: DC TO 2 GHz
VSWR 1.3:1 MAX
- PRODUCT RATINGS:
TEMPERATURE: -40 TO +90 DEG.C
VOLTAGE: 60 VAC
CHARACTERISTIC IMPEDANCE: 50 OHMS
UMCC MATING DURABILITY: 30 CYCLES
FME MATING DURABILITY: 500 CYCLES



1	PC	TUBING, HEAT SHRINK	4
AR	MM	MINIATURE COAX CABLE, 1.37mm OD	3
1	PC	FME PLUG FOR 1.37 OD CABLE	2
1	PC	UMCC TYPE III PLUG	1
QTY	UNIT	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Hao Xiangfeng 28APR05	APVD Paul Zhou 13JUN05		NAME tyco Electronics Tyco Electronics Corporation KunShan, CHINA 215321				
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A4		DATE CODE 00779	DRAWING NO 1750110-2	RESTRICTED TO	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC		± ± ± ± ±		APPLICATION SPEC		SCALE 1:1		SHEET 1 OF 1	REV 0
MATERIAL		FINISH		WEIGHT		RESTRICTED TO			