



Wiha Quality Tools
Germany

[Go To
Image Index](#)


[Go To
Numerical Index](#)

30

Toll Free: (800) 494-6104

The TORXPlus® Advantage

The TorxPlus® Drive System offers 100% improvement in driver bit fatigue & 25% average improvement in driver bit torsional strength. In addition its unique design provides optimum torque transfer and eliminates the need for excessive end load pressure while driving the fastener. The TorxPlus® configuration also virtually eliminates tool "camout" and slippage that can damage the head of the fastener and cause reduced tool life.



Not for use in standard Torx fasteners

- Broad Surface For Driving
- Features 0° Drive Angle Between The Fastener & Driver
- Greater Engagement Depth



Not for use in standard Torx fasteners

362 TORXPlus® Screwdriver With Wiha-SoftFinish Handle Round blade high alloy Chrome-vanadium-molybdenum tool steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
362 11	IP6	60	2.4	3.5	.139	164	6.5	.06	10
362 23	IP7	60	2.4	3.5	.139	164	6.5	.06	10
362 28	IP8	60	2.4	4.0	.157	171	6.7	.10	10
362 29	IP9	60	2.4	4.0	.157	171	6.7	.11	10
362 33	IP10	80	3.1	4.0	.157	191	7.5	.11	10
362 38	IP15	80	3.1	4.0	.157	191	7.5	.11	10
362 39	IP20	100	3.9	4.5	.177	211	8.3	.11	10
362 43	IP25	100	3.9	5.5	.216	211	8.3	.19	10
362 48	IP27	115	4.5	6.0	.236	233	9.2	.20	10
362 53	IP30	115	4.5	7.0	.275	233	9.2	.28	10
362 55	IP40	130	5.1	7.0	.275	254	10.0	.28	10



362 99 Set 7 Pcs. TORXPlus® Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
362 99	362 28	IP8 60	362 43	IP25 100	1.23
	362 33	IP10 80	362 53	IP30 115	
	362 38	IP15 80	362 55	IP40 130	
	362 39	IP20 100			

Wiha T-handle TORXPlus®



Not for use in standard Torx fasteners

[SHOP](#)

364 TORXPlus® Screwdriver, With Wiha-T-handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-T-handle high quality plastic, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
364 61	IP9	100	3.9	4.0	.157	80	3.1	.07	10
364 63	IP10	100	3.9	4.0	.157	80	3.1	.07	10
364 66	IP15	100	3.9	4.0	.157	80	3.1	.07	10
364 69	IP20	100	3.9	4.0	.157	80	3.1	.10	10
364 72	IP25	150	5.9	8.0	.315	120	4.7	.13	10
364 74	IP27	150	5.9	8.0	.315	120	4.7	.14	10
364 76	IP30	150	5.9	8.0	.315	120	4.7	.16	10
364 78	IP40	150	5.9	8.0	.315	120	4.7	.20	10



[SHOP](#)

364 96 Set 6 Pcs. TORXPlus® T-handles

Blade CVM steel, hardened, hard chromed. Chromtop blade tips. Wiha-T-handle high quality plastic, impact resistant.

Item No.	Size	mm	Size	mm	lbs.
364 96	364 63	IP10 100	364 72	IP25 150	1.01
	364 66	IP15 100	364 74	IP27 150	
	364 69	IP20 100	364 76	IP30 150	



[SHOP](#)

362 96 Set 6 Pcs. TORXPlus®

Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
362 96	362 11	IP6 60	362 29	IP9 100	.72
	362 23	IP7 80	362 33	IP10 115	
	362 28	IP8 80	362 38	IP15 130	

[PREVIOUS](#)

[NEXT](#)