


ISORYL SCREWDRIVERS

▼ AG FOR SLOTTED HEADS - FORGED BLADES

- Optimum tip grain structure for exceptional torsional strength.
- Polished chrome finish.


	e x A mm	T mm	Ø1 x L1 mm	Ø2 x L2 mm	L mm	ΔΔ g
AG.5.5X100	1,0 x 5,5	0,6	5 x 100	28 x 100	200	67
AG.5.5X150	1,0 x 5,5	0,6	5 x 150	28 x 100	250	75
AG.6.5X150	1,2 x 6,5	0,7	6 x 150	30 x 110	260	108
AG.8X150	1,2 x 8,0	0,7	7 x 150	30 x 110	360	123
AG.8X200	1,2 x 8,0	0,7	7 x 200	30 x 110	310	139
AG.8EX200	1,6 x 8,0	1,0	8 x 200	34 x 120	320	191
AG.10X200	1,6 x 10,0	1,0	9 x 200	34 x 120	320	219
AG.10X250	1,6 x 10,0	1,0	9 x 250	34 x 120	370	242



▼ AGT FOR SLOTTED HEADS - FORGED BLADES - TEE-HANDLE

- High torque capability.
- Chrome finish.

	e x A mm	T mm	L2 x L3 mm	Ø1 x L1 mm	L mm	ΔΔ g
AGT.8X100	1,2 x 8,0	1,0	30 x 85	8 x 100	130	150
AGT.10X100	1,6 x 10,0	1,0	30 x 85	10 x 100	130	160



▼ ARB FOR SLOTTED HEADS - SHORT BLADES

- For use in confined spaces.
- Polished chrome finish.

	e x A mm	T mm	Ø1 x L1 mm	Ø2 x L2 mm	L mm	ΔΔ g
ARB.4X40	0,8 x 4,0	0,5	4,0 x 40	29 x 50	90	38
ARB.5.5X40	1,0 x 5,5	0,6	5,5 x 40	29 x 50	90	39
ARB.6.5X40	1,2 x 6,5	0,7	6,5 x 40	29 x 50	90	42

