




CU01 Series USB Type-A Right Angle DIP Receptacle Connector

- ④ 4 position shielded receptacle connector
- ④ DIP Straight angle through hole
- ④ 2mm centerline and 2.5mm centerline power contacts
- ④ High durability and long cycle life





:E159616

P/N CU01S*H*S00



P/N CU01S*H*D00



Ordering Code

① CU ② 0 ③ 1 ④ S ⑤ A ⑥ H ⑦ 1 ⑧ S ⑨ 0 ⑩ 0

① Series No.

② S= Socket

③ Plating code:

A= Selective Gold flash over 50μin Nickel on contact area

C= Selective 30μin Gold over Nickel on contact area

P= Selective Gold flash over 28μin PI-NI on contact area

④ Tail style:

H = Right angle DIP

⑤ Insulator color:

1= Black ; 0=White

⑥ Type:

S= Single port

D= DUAL port

⑦ Options:

00= Standard

*Special option Consult manufacturer