

Pluggable Screw Terminal Block

180° Wire Entry

Specifications:

Application	Used with 5mm socket available with Sonalert® Solution models.
Electrical	Max Voltage: 300V Max Current: 15 Amp
Screw Terminal	Tightening Torque: 8 in-lbs
Connection strength	Minimum of 5 lbs to remove pluggable screw terminal block from socket of Sonalert device.
Operating Temperature	Max 110°C
Material	Housing: UL94V0 Polymide (Color Black) Screw: Steel / Zinc chromate
Wire Range	12 to 26 AWG
Wire Strip Length	¼ inch or 6mm
Dimensional Tolerances	1 place = $\pm .3$ mm 2 places = $\pm .01$ inch or $\pm .13$ mm 3 places = $\pm .005$ inch or $\pm .038$ mm

Dimensions: Inches (mm)**Flame Retardant****RoHS Compliant**