


DESCRIPTION: DIP SOLDER MALE/STAMPED



#### SPECIFICATIONS:

#### MATERIALS:

SHELL: STEEL, TIN PLATED

INSULATOR: UL 94V-0 RATED BLACK PBT  
+30% FIBER-GLASS OR NYLON-66

#### ELECTRICALS:

CURRENT RATING: 5 AMPS


CONTACT RESISTANCE: 15 mOHMS MAX

INSULATOR RESISTANCE: 1000 MOHMS MIN

VOLTAGE: 500V AC FOR 1 MINUTE

TEMPERATURE: -50°C TO +100°C

| POS. | A     | B     | C     | D     | E     | F     | G     |
|------|-------|-------|-------|-------|-------|-------|-------|
| 9    | 1.213 | 0.984 | 0.666 | 0.756 | 0.329 | 0.109 | 0.496 |
|      | 30.80 | 24.99 | 16.92 | 19.20 | 8.36  | 2.77  | 12.60 |
| 15   | 1.543 | 1.312 | 0.994 | 1.091 | 0.329 | 0.109 | 0.496 |
|      | 39.19 | 33.32 | 25.25 | 27.70 | 8.36  | 2.77  | 12.60 |
| 25   | 2.087 | 1.852 | 1.534 | 1.618 | 0.329 | 0.109 | 0.496 |
|      | 53.00 | 47.04 | 38.96 | 41.10 | 8.36  | 2.77  | 12.60 |
| 37   | 2.732 | 2.500 | 2.181 | 2.256 | 0.329 | 0.109 | 0.496 |
|      | 69.30 | 63.50 | 55.42 | 57.30 | 8.36  | 2.77  | 12.60 |
| 50   | 2.638 | 2.406 | 2.079 | 2.169 | 0.445 | 0.109 | 0.606 |
|      | 67.00 | 61.00 | 52.80 | 55.10 | 11.30 | 2.77  | 15.39 |



171-XXX-112-001

SERIES \_\_\_\_\_

POSITIONS \_\_\_\_\_

009  
015  
025  
037  
050

GENDER \_\_\_\_\_

1 = MALE  
2 = FEMALE

TERMINATION \_\_\_\_\_

1 = DIP SOLDER

SHELL PLATING \_\_\_\_\_

2 = TIN

HARDWARE OPTIONS \_\_\_\_\_

00 = NO HARDWARE  
01 = .098 4-40 CLINCH NUT BOARD SIDE  
02 = .250 4-40 CLINCH NUT BOARD SIDE  
03 = .250 4-40 CLINCH NUT MATING SIDE  
91 = .225 4-40 SPACER/BOARD LOCK

PLATING OPTIONS \_\_\_\_\_

1 = GOLD FLASH  
2 = 30 MICRO-INCH GOLD



THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF NorComp AND  
SHALL NOT BE REPRODUCED, COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OR SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.

DRAWN:

**PAM JENKINS**

DATE:

**8-12-98**

CHECKED:

DATE:

SCALE:

SHEET 1 OF 2 REV 5


DWG NO.

171-XXX-112-XX1


**NorComp**

DESCRIPTION: CLINCH NUT HARDWARE


ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS




03X..... .250" (MATING SIDE) - CN8



02X ..... .250" (BOARD SIDE) - CN2



01X ..... .098" (BOARD SIDE) - CN1





91X ..... .225" (BOARD SIDE) - .197 MATING SIDE - CN10/SFS0440  
NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

|                                                                                      |                                                                                                                                                                                             |                            |              |                  |       |
|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|--------------|------------------|-------|
|  | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | DRAWN:<br>WAYNE ROBBINS    |              | DATE:<br>8-23-98 |       |
|                                                                                      |                                                                                                                                                                                             | CHECKED:<br>PAM JENKINS    |              | DATE:<br>8-24-98 |       |
|  |                                                                                                                                                                                             | SCALE:                     | SHEET 1 OF 1 |                  | REV 1 |
|                                                                                      |                                                                                                                                                                                             | DWG NO. CLINCH-NUT OPTIONS |              |                  |       |

DESCRIPTION:

| POS |                       | H                     |
|-----|-----------------------|-----------------------|
| 9   | <u>.984</u><br>25.00  | <u>.433</u><br>10.99  |
| 15  | <u>1.312</u><br>33.32 | <u>.757</u><br>19.23  |
| 25  | <u>1.852</u><br>47.04 | <u>1.305</u><br>33.15 |
| 37  | <u>2.500</u><br>63.50 | <u>1.957</u><br>49.71 |
| 50  | <u>2.406</u><br>61.11 | <u>1.740</u><br>44.20 |



|                                                                                      |                                                                                                                                                                                             |                       |                                 |                  |         |          |
|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|---------------------------------|------------------|---------|----------|
|  | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | DRAWN:<br>PAM JENKINS |                                 | DATE:<br>3-30-01 |         |          |
|                                                                                      |                                                                                                                                                                                             | CHECKED:              |                                 | DATE:            |         |          |
|  |                                                                                                                                                                                             |                       | SCALE:                          | SHEET<br>2       | OF<br>2 | REV<br>4 |
|                                                                                      |                                                                                                                                                                                             |                       | DWG NO. DSUB VERTICAL FOOTPRINT |                  |         |          |