


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		A1	REV PER ECR 10-016092	09AUG10	JR	TM

D

C


B

A



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
26-22 AWG STRANDED	NOT LISTED	NOT CERTIFIED

- 1 STAMP 6S AMP APPROX AS SHOWN
6S INDICATES STUD SIZE
- 2 PHOSPHOR BRONZE PER ASTM B103, ANNEALED



52734

B

A

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 2-15-93 TA BRINKMAN		Tyco Electronics Corporation Harrisburg, PA 17105-3608				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A	DIMENSIONS: MM [INCHES] 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK 2-15-93 DA PATTERSON	APVD 2-15-93 JL MECKLEY	NAME						
	FOR APPLICATION	TOOLING ASSISTANCE CENTER				CIRCULAR MIL AREA: 0.10-0.41mm² [202-810] STRANDED		PRODUCT SPEC —	TERMINAL, LONG SPRING SPADE, BUDGET —					
	TOOLING INFORMATION 1-800-722-1111		MATERIAL			APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH TIN PLATE PER ASTM B545		WEIGHT —		A2 00779 C=52734				
						CUSTOMER DRAWING			SCALE 10:1		SHEET 1 of 1		REV A1	