






Belegungsplan Loading-Plan


Schirm Shield

1	Gelb yellow	1
2	Orange orange	2
3	Weiß white	3
6	Blau blue	6
1	Schwarz SW1 black	1
2	Schwarz SW2 black	2
3	Schwarz SW3 black	3
4	Schwarz SW4 black	4



Kabelschnitt Cablecut

5:1



Übertragungseigenschaften nach ISO/IEC 11801:2002: Class D
Schutzart: IP67
Temperaturbereich: -20°C ...+70°C

Transmission properties in accordance with ISO/IEC 11801:2002: Class D
Protection level: IP67
Temperature range: -20°C ...+70°C

09 45 725 1361	100 m
09 45 725 1356	50 m
09 45 725 1353	20 m
09 45 725 1351	10 m
09 45 725 1327	5 m
09 45 725 1325	3 m
09 45 725 1323	1,5 m
Bestell-Nr. Part-No.	Maß a Dimension a

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances			
				Dat.	Name	Maßstab/Scale 2:1 5:1	RJ1 Kabel IP67 Hybrid, flexibel <i>RJ1 Cable IP67 Hybrid, stranded</i> <i>AWG22/7, 2xRJ45, 4xPower</i>					
			Detail.	17.08.04	Wie							
			Insp.	17.08.04	Wae							
			Stand.									
32192			HARTING Electronics GmbH & Co. KG						TB 09 45 725 1323			Blatt/ page /
Mod. Dat. Name			D-32339 ESPELKAMP									
									Sub.			