

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080146](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway 40W Fluorescent Machine Light, Screw Mount with 18/3 SJTOOW Cord Type, Overall Cord Length 4.57m (15.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
UL E174254

General

Product Family Portable Lighting
Series [130108](#)
NEMA Configuration NEMA 5-15
Outlet None
Overview [Wide-Area Lighting Products](#)
Product Name Super-Safeway
Type Wide Area Lamps
UPC 78678861263

Physical


Cord Length - Primary 4.57m (15.0')
Cord Length - Secondary N/A
Depth 76.20mm (3.000")
Duty Industrial
Guard Included No
Guard Type N/A
Height 57.15mm (2.250")
Length 798.83mm (31.450")
Material - Globe Clear Polycarbonate
Material - Guard Nitrile Rubber 80 Shore A
Mounting Style Screw-Bracket
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 18/3 SJTOOW
Lamp Type PL-L 40/41
Lamp Wattage - Maximum 40W
Lumens 2970
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1097-3M



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130108](#) Series