



250 SOFT-PLUS

Safety hammer with maleable cast iron shells

Interchangeable heads and hickory handle. Slots in the head and grooves in the shells provide an absolute safe connection. The screw is guided through the handle and connected with a self-locking nut. This provides highest safety.

Blue (R) = soft 20 Shore D

Material: Elastomer

For sensitive work pieces, light metal production, furniture industry, assembly works, etc.

Black (S) = medium soft 45 Shore D

Material: Caoutchouc

For sturdy applications, pavement craft, etc.

Yellow (G) = medium hard 63 Shore D

Material: Polyurethane

For universal applications, tooling and machine industry, automotive workshops, sheet metal work, etc.

Anthracite (A) = hard 70 Shore D

Material: Polyurethane

For high striking power, road building, etc

250 Safety hammer SOFT-PLUS

Code	No.	mm	L mm	Ø mm	mm	PU
1445820	250 AA-30	87	290	30	330	6
1445839	250 AA-40	110	325	40	650	6
1446010	250 AB-30	87	290	30	330	6
1446029	250 AB-40	110	325	40	650	6
1445936	250 AG-30	87	290	30	330	6
1445960	250 AG-40	110	325	40	650	6
1446088	250 AS-30	87	290	30	330	6
1446118	250 AS-40	110	325	40	650	6
1445790	250 BB-30	87	290	30	330	6
1445804	250 BB-40	110	325	40	650	6
1445898	250 BG-30	87	290	30	330	6
1445901	250 BG-40	110	325	40	650	6
1446045	250 BS-30	87	290	30	330	6
1446053	250 BS-40	110	325	40	650	6
1445766	250 GG-30	87	290	30	330	6
1445774	250 GG-40	110	325	40	650	6
1445987	250 GS-30	87	290	30	330	6
1445995	250 GS-40	110	325	40	650	6
1445855	250 SS-30	87	290	30	330	6
1445863	250 SS-40	110	325	40	650	6

E 250 Spare head SOFT-PLUS

For safety hammer 250. Cadmium free, splinter-proof, shatter-proof, wear-resistant, colour fast.

Code	No.	Ø mm	mm	PU
1445200	E 250 A-30	30	20	1
1445219	E 250 A-40	40	45	1
1445111	E 250 B-30	30	20	1
1445154	E 250 B-40	40	45	1
1445170	E 250 G-30	30	20	1
1445189	E 250 G-40	40	45	1
1445235	E 250 S-30	30	20	1
1445243	E 250 S-40	40	45	1