




DEGSON ELECTRONICS CO., LTD.

Product Specification



DG332K-5.0



Material

Screws	:	M2.5 steel Zinc plated
Wire guard:		Phosphor bronze, Ni plated
Contact	:	Brass, Tin plated
Housing	:	PBT, UL94V-0

Electrical

Rated voltage	:	300V
Rated current	:	10A
Contact resistance	:	20m Ω
Insulation resistance	:	5000M Ω /DC1000V
Withstanding voltage	:	AC2000V/1Min
Wire range	:	28-16AWG 1.5mm ²

Mechanical

Temp. Range	:	-30°C~+120°C
Torque	:	0.4Nm(3.6lb.in)
Strip length	:	4.5mm

HOW TO ORDER:

DG332K-5.0 - **P** - -

X	X	X
Customer Request		

Series No. **No of Pole** **Color**

1 Gray	4 Green	7 Trans- parent
2 Blue	5 Orange	8 Yellow
3 Black	6 Red	9 White



DEGSON ELECTRONICS CO., LTD.

NAME

DG332K-5.0