



Wiha Quality Tools
Germany

Go To
Image Index

Go To
Numerical Index

20

Toll Free: (800) 494-6104

Wiha TORX® MicroFinish Handle Non-Slip Grip

Wiha MicroFinish handle has a patented non-slip surface - it won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. You get maximum force and comfort with dry, oily or wet hands.

Safe, high density material,
eliminates risk of sharp objects
becoming embedded in the handle

Blades are hardened
& hard chromed

Exact
fit precision
ground tips



MicroFinish Handle with patented
non-slip surface. Ergo handle
shape for maximum comfort &
exceptional torque transfer

Blade CVM, hardened & tempered tool
steel, gives exceptional tool life, wear
resistance & high torque performance



527 TORX® Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
527 11	T9	60	2.4	4.0	.157	171	6.7	.15	10
527 13	T10	80	3.1	4.0	.157	191	7.5	.15	10
527 16	T15	80	3.1	4.0	.157	191	7.5	.15	10
527 19	T20	100	3.9	4.0	.157	211	8.3	.15	10
527 22	T25	100	3.9	4.5	.177	211	8.3	.16	10
527 26	T27	115	4.5	5.5	.216	233	9.2	.25	10
527 29	T30	115	4.5	6.0	.236	233	9.2	.27	10
527 32	T40	130	5.1	7.0	.275	254	10.0	.40	10



**See MicroFinish Non-Slip Grip
Screwdrivers On Page 73-74**



527 90 Set 5 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item											
No.		Size		mm		Size		mm		lbs.	
527 90	527 13	T10		80		527 22	T25		100		1.0
	527 16	T15		80		527 29	T30		115		
	527 19	T20		100							



527 91 Set 8 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

Item						
No.		Size	mm	Size	mm	lbs.
527 91	527 11	T9	60	527 22	T25	100
	527 13	T10	80	527 26	T27	115
	527 16	T15	80	527 29	T30	115
	527 19	T20	100	527 32	T40	130

PREVIOUS

NEXT