


5N Type Side-operational 4R Light Touch Switches

Type: **EVQPC**

■ Features


- Wealth of product types: Horizontal type, snap-in terminals, etc.
- Can be automatically dip-soldered: Integral molding of the terminals and main body prevents the escape of flux.




■ Recommended Applications

- Operating switches for electronic equipment

■ Explanation of Part Numbers



■ Specifications

Type		Snap action/Push-on type SPST	
Electrical	Circuit Diagram		
	Rating	10 μ A 2 Vdc to 20 mA 15 Vdc (Resistiv load)	
	Contact Resistance	50 m Ω max.	
	Insulation Resistance	50 M Ω min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 8 ms max. (OFF)	
Mechanical	Operating Force	1.0 N $\pm$ 0.4 N 1.3 N $\pm$ 0.4 N 1.6 N $\pm$ 0.5 N	2.6 N $\pm$ 0.6 N
	Travel	0.25 mm $\pm$ 0.10 mm	
Endurance	Operating Life	100000 cycles min.*	50000 cycles min.
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/Packing Unit		700 pcs. Radial Taping (Reel Pack)	
Quantity/Carton		7000 pcs.	



*1 million cycles also available, consult our salesmen.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

■ Dimensions in mm (not to scale)

EVQPC



Part Numbers	Operating Force	Push Plate Place	Push Plate Color	Operating Life	Insert Machine	H ⁰ Dimension
EVQPC005K	1.0 N	4.75 mm	Black	100000 cycles	Panasert	20 mm
EVQPC105K	1.3 N	4.75 mm	Black	100000 cycles	Panasert	20 mm
EVQPC205K	1.6 N	4.75 mm	Black	100000 cycles	Panasert	20 mm
EVQPC305K	2.6 N	4.75 mm	Black	50000 cycles	Panasert	20 mm
EVQPC405K	1.0 N	4.75 mm	Black	100000 cycles	Avisert	21 mm
EVQPCP05K	1.3 N	4.75 mm	Black	100000 cycles	Avisert	21 mm
EVQPC605K	1.6 N	4.75 mm	Black	100000 cycles	Avisert	21 mm
EVQPC705K	2.6 N	4.75 mm	Black	50000 cycles	Avisert	21 mm

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[EVQ-PC005K](#) [EVQ-PC105K](#) [EVQ-PC205K](#) [EVQ-PC305K](#) [EVQ-PC405K](#) [EVQ-PC505K](#) [EVQ-PC705K](#) [EVQ-PCP05K](#)