

Heatsinks f.cool

Cases f.case

Connectors f.con

Sockets

PCB connectors

Male headers

Female headers

Direct female connectors

Jumpers

IDC-connectors

D-Sub connectors

Brackets for PC

Optoelectronics

Male headers

SL 3 ... / SLK 3 ...

SL 3 053 36 Z

male header □ 0.635 mm, "dimensions A + B" changeable

Data sheet

add to request



Features

Technical Drawing

Variants

Service

Accessories / related products

grid	2.54 mm
no. of contacts	36
contact material	CuSn alloy
surface of contact	tin-plated
surface contact /	Ni+≥0.2µm Au
contact sleeve	Ni+4...6µm Sn
version	"dimensions A + B" changeable
volume resistance	≤5 mΩ
nominal current	3 A
nominal voltage	250 V AC
test voltage	2000 V
insulating body material	PA 4.6. GF
temperature range	-40°C... +163°C (260°C/10 s)
class of flammability	UL 94 V-0
specific insulation resistance	>10.0 ⁷⁰ Ω·m
connection type	-
reflow solderable	yes