


* 434-188 → 434-231

0510 SADDLE TYPE TIE MOUNTS





- Material: UL approved NYLON 66, 94V-2
- To apply with KSS nylon cable ties:
 - HC-0: CV-075, 094, ... 280, 310
 - HC-1: CV-075, 094, ... 280, 310
 - HC-2: All applicable sizes
- Saddle design provide maximum stability to wire bundles.
- To apply, simply fix mount with a screw and secure wire bundles with KSS nylon cable ties.

Unit: mm

Item No.	H	L	W	T	B	Packing
HC-0	5	19	9.5	5	3.4	100pcs
HC-1	7	15	10	5	3	
HC-2	9	23	16	9	6	

0512 PUSH TIE MOUNT




- Material: UL approved NYLON 66, 94V-2
- Drill 6.2mm hole on board to fix tie mount and then insert tie into the mount for bundling cables.

Unit: mm

Item No.	T	FITING	Packing
PHC-4	4.0	4.8	100pcs
PHC-8	8.1	6.2	

0515 SELF-ADHESIVE CABLE CLAMP



- Material: UL approved Black NYLON 66, 94V-2 (Backed with adhesive tape)
- Backed with a high quality tape. Designed to secure wire bundles where fixing holes are impractical. Can be quickly applied to almost any clean, smooth and grease-free surface. (Also provided with a mounting hole)
- Color: Black

Unit: mm

Item No.	Aφ	Bφ	T ₁	T ₂	L	W	H	Packing
4J-S	6	4.4	1.1	2.0	25.8	13.4	9.1	100pcs.
6J-S	9	4.4	1.1	3.0	29.4	13.4	14.0	
8J-S	12	4.4	1.5	3.0	35.5	16.4	16.5	
10J-S	14	4.4	1.5	3.0	36.5	16.4	18.5	
11J-S	16	4.4	1.5	3.0	38.5	16.4	20.5	
12J-S	18	4.4	1.5	3.0	42.0	16.4	22.5	

