


A



B


C

Electrical Test:

1. 100% short, open, miswire test
2. Contact Resistance: 2Ω Max.
3. Insulation Resistance: 5Ω Min.

D

⑤	OUTER MOLD: PVC 45P COLOR BEIGE(CS-B02)
④	INNER MOLD: PE COLOR TRANSPARENT
③	CONNECTOR: USB A JACK SOLDER TYPE INSULATION: WHITE.
②	CONNECTOR: USB A PLUG SOLDER TYPE INSULATION: WHITE.
①	CABLE: UL2725 28AWG*1P+24AWG*2C+A.D+B65% O.D:4.7MM PVC JACKET COLOR BEIGE(CS-B02)
NO.	DESCRIPTION



E

F

G



Scale	1:1							Name
TOLERANCE						Drawn	08.29.11	Chappel
X.X	±0.40					Approved		
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°					 		
			Modification	Date	Name			

Item No.	AK669-18-R (1.8 Meters)
	AK669-30-R (3.0 Meters)
	AK669-50-R (5.0 Meters)

Title	USB Extention Cable Version 1.1, USB A Male to USB A Female
--------------	--

Drawing No.

rev00

Replace

Sheet

H