

## HC-EVO-B24-SHFDC-2SSM40-PLRBK

Order No.: 1407666



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407666>

HEAVYCON EVO box mounting base, plastic, B24, with double locking latch, height: 84 mm, with gland, 2 x M40, one of the two openings for the screw connections is sealed but can be broken open using a screwdriver, with protective cover.

### Commercial data

|                        |  |
|------------------------|--|
| EAN                    | <br>4 046356 777292 |
| Pack                   | 1  |
| Customs tariff         | 85389099   |
| Gross weight in pieces | 228.60 g   |
| Country of Origin      | PL   |

### Product notes

WEEE/RoHS-compliant since:  
03/07/2012



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General data

|        |   |
|--------|---|
| Note   | For contact inserts HC-B24, BB46, D64, DD108, M |
| Design | B24   |
| Height | 84 mm   |
| Width  | 57 mm   |

|   |   |
|---|---|
| Length                                  | 144 mm  |
| Housing type                            | Box mounting bases  |
| Color                                   | black   |
| Locking type                            | For double locking latch  |
| No. of cable exits                      | 2   |
| Cable exit                              | Lateral   |
| Type of the screw connection            | 2x M40  |
| Protective cover                        | Yes   |
| Degree of protection for housing        | IP65  |
| Ambient temperature (operation)         | -40 °C ... 125 °C   |
| Housing material                        | Polyamide   |
| Seal material                           | NBR   |
| Material, protective cover              | Polyamide   |
| Inflammability class according to UL 94 | V0  |
| Connection                              | One of the two openings for the screw connections is sealed but can be broken open using a screwdriver. |

## Certificates

Certification

Certifications applied for:

Certification Ex:

---

## Accessories


| Item | Designation | Description |
|------|-------------|-------------|
|------|-------------|-------------|

### General

|         |                      |   |
|---------|----------------------|---|
| 1407696 | HC-B10-24-DL-PLBK    | Replacement double locking latch for HEAVYCON EVO housing, HC-B10/HC-B16/HC-B24, PA                                   |
| 1407705 | HC-B24-SG-RBK        | Replacement flat gasket for HEAVYCON EVO supporting base element type B24   |
| 1407701 | HC-B24-SL-PLBK       | Replacement single locking latch for HEAVYCON EVO housing type B24, PA  |
| 1407709 | HC-B24-SP-RBK        | Profile gasket for HEAVYCON EVO supporting base element type B24  |
| 1407674 | HC-K-KV-M40(16-28)BK | Plastic screw connection up to 5 bar, thread length: 10 mm, cable diameter: 16 - 28 mm, WAF 46, screw connection: M40 |

## Drawings

Dimensioned drawing



Dimensional drawing

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG, England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;