

Distributed by:




JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 837222

LOC	DIST	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
AG	53				T	REV PER 063C-0653-04			18JAN04	MM



- 1 MATERIAL:
HOUSING: FLAME RETARDANT NYLON, 94V-0,
OR FLAME RETARDANT POLYESTER 94V-0.
CONTACT: PHOSPHOR BRONZE.
- 2 CONTACT PLATED WITH 0.00076 [0.000030] GOLD INLAY OVER
0.00076 [0.000030] NICKEL IN CONTACT AREA ONLY.
- 3 CONTACT PLATED WITH 0.0013 [0.000050] GOLD INLAY OVER
0.00076 [0.000030] NICKEL IN CONTACT AREA ONLY.
- 4 CONTACT PLATED WITH 0.0025 [0.000100] TIN OVER ALL.
- 5 CONTACT PLATED WITH 0.00038 [0.000015] GOLD INLAY OVER
0.00076 [0.000030] NICKEL IN CONTACT AREA ONLY.
6. HOUSING CUT-OFF BURR NOT EXCEED 0.13 [0.005].
7. CONNECTOR MATES WITH 0.61 [0.024] TO 0.66 [0.026] SQUARE
PIN. PIN LENGTH 4.45 [0.175] MIN. TO 8.38 [0.330] MAX.
- 8 CONTACT PLATED WITH 0.0025 [0.000100] MATTE TIN OVER ALL.

OBSOLETE	8	BLACK	4-530153-1
	5	BLACK	3-530153-2
OBSOLETE	4	BLACK	2-530153-2
		NATURAL	2-530153-1
OBSOLETE	3	BLACK	1-530153-2
OBSOLETE	2	RED	1-530153-0
OBSOLETE		BLUE	530153-6
OBSOLETE		YELLOW	530153-4
OBSOLETE		BLACK	530153-2
OBSOLETE		NATURAL	530153-1

		FINISH	HOUSING COLOR	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.25 [0.010] 3 PLC DEC ± - ANGLES ± - MATERIAL 1		AMP AMP Incorporated Harrisburg, PA 17105-3608		
		NAME		
		TANDEM SPRING SHUNT CONNECTOR 2 POSITION, 2.54 [0.100] CL		
		108-9062		
FINISH SEE TABLE	APPLICATION SPEC 114-1045	SIZE C	CAGE CODE 00779	DRAWING NO 530153
	WEIGHT -	SCALE 10:1	SHEET 1 OF 1	