




ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	FLPV2-XX	Flexible Light Pipe 2mm Adapter, Vertical w/ LED, See page 2
2	1	FLP25-XX.X	Flexible Light Pipe Lens Cap Assembly, 2mm

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	09/14/09	T. Y.
B	Replaced 3UWC-0.6K-F with 3UWC1.035C-F	04/26/12	T. Y.
C	Updated Table For Length "L"	11/16/12	T. Y.

NOTE: FLPV2-XX ADAPTER SHIPPED NON-ASSEMBLED



SHORT LEAD CATHODE	LED PART NO.	LONG LEAD CATHODE
RED	3xBCC-F	GREEN
YELLOW	3xBCC-Y/G-F	GREEN
RED	3xBCC-R/Y-F	YELLOW
AMBER	3xBCC-A/G-F	GREEN

ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

REVERSE VOLTAGE	5V
REVERSE CURRENT	100uA
OPERATING TEMPERATURE RANGE	-25° C - 85° C
STORAGE TEMPERATURE	-30° C - 100° C
LEAD SOLDERING TEMPERATURE(1/16" FROM BODY)	260° C FOR 5 SECONDS

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ±.1	X° ± 1°		
.XX ±.02			
.XXX ±.010			
DESIGNED: Brian Oliver	DATE: 09/14/09	TITLE: FLEXIBLE LIGHT PIPE ASSY, 7mm ROUND, VERTICAL	
CHECKED: Fred Jensen	DATE: 09/14/09	PART NO: FLP25VX.X-XX	REVISION: C
		CAGE CODE : 32559	SHEET # 1 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[FLP25V1.5-SA](#) [FLP25V1.5-SUG](#) [FLP25V1.5-SUR](#) [FLP25V1.5-UBW](#) [FLP25V10.0-SA](#) [FLP25V10.0-SUG](#)
[FLP25V10.0-SUR](#) [FLP25V10.0-UBW](#) [FLP25V10.0-UW](#) [FLP25V10.5-SA](#) [FLP25V10.5-SUG](#) [FLP25V10.5-SUR](#)
[FLP25V10.5-UBW](#) [FLP25V10.5-UW](#) [FLP25V11.0-SA](#) [FLP25V11.0-SUG](#) [FLP25V11.0-SUR](#) [FLP25V11.0-UBW](#)
[FLP25V11.0-UW](#) [FLP25V11.5-SA](#) [FLP25V11.5-SUG](#) [FLP25V11.5-SUR](#) [FLP25V11.5-UBW](#) [FLP25V11.5-UW](#)
[FLP25V12.0-SA](#) [FLP25V12.0-SUG](#) [FLP25V12.0-SUR](#) [FLP25V12.0-UBW](#) [FLP25V12.0-UW](#) [FLP25V2.0-SA](#)
[FLP25V2.0-SUG](#) [FLP25V2.0-SUR](#) [FLP25V2.0-UBW](#) [FLP25V2.0-UW](#) [FLP25V2.5-SA](#) [FLP25V2.5-SUG](#) [FLP25V2.5-](#)
[SUR](#) [FLP25V2.5-UBW](#) [FLP25V2.5-UW](#) [FLP25V3.0-SA](#) [FLP25V3.0-SUG](#) [FLP25V3.0-SUR](#) [FLP25V3.0-UBW](#)
[FLP25V3.0-UW](#) [FLP25V3.5-SA](#) [FLP25V3.5-SUG](#) [FLP25V3.5-SUR](#) [FLP25V3.5-UBW](#) [FLP25V3.5-UW](#) [FLP25V4.0-SA](#)
[FLP25V4.0-SUG](#) [FLP25V4.0-SUR](#) [FLP25V4.0-UBW](#) [FLP25V4.0-UW](#) [FLP25V4.5-SA](#) [FLP25V4.5-SUG](#) [FLP25V4.5-](#)
[SUR](#) [FLP25V4.5-UBW](#) [FLP25V4.5-UW](#) [FLP25V5.0-SA](#) [FLP25V5.0-SUG](#) [FLP25V5.0-SUR](#) [FLP25V5.0-UBW](#)
[FLP25V5.0-UW](#) [FLP25V5.5-SA](#) [FLP25V5.5-SUG](#) [FLP25V5.5-SUR](#) [FLP25V5.5-UBW](#) [FLP25V5.5-UW](#) [FLP25V6.0-SA](#)
[FLP25V6.0-SUG](#) [FLP25V6.0-SUR](#) [FLP25V6.0-UBW](#) [FLP25V6.0-UW](#) [FLP25V6.5-SA](#) [FLP25V6.5-SUG](#) [FLP25V6.5-](#)
[SUR](#) [FLP25V6.5-UBW](#) [FLP25V6.5-UW](#) [FLP25V7.0-SA](#) [FLP25V7.0-SUG](#) [FLP25V7.0-SUR](#) [FLP25V7.0-UBW](#)
[FLP25V7.0-UW](#) [FLP25V7.5-SA](#) [FLP25V7.5-SUG](#) [FLP25V7.5-SUR](#) [FLP25V7.5-UBW](#) [FLP25V7.5-UW](#) [FLP25V8.0-SA](#)
[FLP25V8.0-SUG](#) [FLP25V8.0-SUR](#) [FLP25V8.0-UBW](#) [FLP25V8.0-UW](#) [FLP25V8.5-SA](#) [FLP25V8.5-SUG](#) [FLP25V8.5-](#)
[SUR](#) [FLP25V8.5-UBW](#) [FLP25V8.5-UW](#) [FLP25V9.0-SA](#)