




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₁	REVISED	KYLE 9-24-97	 10/21/97

ELECTRICAL SPECIFICATIONS

FREQ.	VSWR (MAX)
Dc-18.0 GHz	1.22:1
18.0-26.5 GHz	1.28:1

.XXX = in
XX.X = mm (REF)

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204			
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A			
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204			
EMI GASKET	CONDUCTIVE ELASTOMERS PER MIL-G-83528	N/A			
COMPONENT	MATERIAL	FINISH			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY DAC	DATE 2-27-87	 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
	CHECKED BY FM	12-16-88			
	APPD BY FM	12-16-88			
FRAC. ± 1/64	DEC. ±.005	ANGLES ± 1°	TITLE "OS-50P" PLUG TO "OSM" JACK ADAPTER		
These drawings and speci- fications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale o f item(s) without written permission.					
USE ASS'Y PROCEDURE NO. A.P. N/A					
SIZE B			CODE IDENT NO. 26805	8782-2200-00	REV 01 ₁
SCALE 8:1					SHEET 1 OF 1

CUSTOMER DRAWING

AMP PART # 1063476-1
SHEET 1 OF 1 REV A