

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1206150005](#)
Status: **Active**
Overview: Brad Ultra-Lock (M12) EX Connection System for Zone 2 Hazardous Locations
Description: Ultra-Lock (M12) EX Receptacle, 4 Poles, 1/4 - 18 NPT, Female (Straight) to 22 AWG PVC Cable, 0.30m (11.81") Length



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Receptacles
Series	120615
IP Rating	IP69K
NEMA Rating	NEMA 6
Overview	Brad Ultra-Lock (M12) EX Connection System for Zone 2 Hazardous Locations
Product Name	Ultra-Lock (M12) EX
Type	Single Ended (pigtail)
UPC	78172535793
Physical	
Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	1/2" - 14 NPT
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	22
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	125V
Material Info	
Engineering Number	LWR4A00A18C300
Reference - Drawing Numbers	
Sales Drawing	SD-120614-999, SD-120615-002

EU ELV Not Relevant	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120615 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION