




SECTION A-A



P.C.B. LAYOUT

Materials:

Housing material: pps+40% Glass-filled(UL-94v-0)

Color: Brown

Contact material: phosphor-bronze

Plating:

Contact: 3.8um(150uin.)min tin-lead

Solder tail: 2.5um(100uin.)min tin-lead

Underplante: 1um(40uin.)min nickel

Contact resistance:

Surface-mount: 20m ohm

Through-mount: 30m ohm

Insulation resistance: 10000M ohm min

Withstanding voltage: 600v ac

Current rating: 1amp continuous

Voltage rating: 120V ac

NO. OF CONTACTS	A±0.2	B±0.2	C±0.1	D±0.1	E±0.2
20	15.66	15.66	5.08	5.08	17.28
28	18.20	18.20	7.62	7.62	20.87
32	18.20	20.74	7.62	10.16	22.76
44	23.28	23.28	12.70	12.70	28.05
52	25.82	25.82	15.24	15.24	31.65
68	30.90	30.90	20.32	20.32	38.83
84	35.98	35.98	25.40	25.40	46.00

HOW TO ORDER:

6601-XX-01: STANDARD SMD W/O PEGS

multicomp

DESCRIPTION:

SMD PLCC SOCKET

SIZE

A4

PART NO:

6601-XX-01

DRAWN:

Jerry Chen

CHECKED:

APPROVAL:

GENERAL TOLERANCE:

.X=±0.2


.XX=±0.15

UNIT: MM

SCALE:

SHEET: 1 / 1

PROJECTION:



E			
D			
C			
B			
A	12-09-2002		JACK
REV	DATE	FILE	BY