



BANANA JACK

09-9124-1-0210 (BLK) PHONE TIP JACK 09-9124-1-0212 (RED) INSULATED

ACCEPTS .080 DIA.
PROBE




7/16" dia. molded nylon head in choice of colors (red or black), Nickel plated brass body. Phosphor bronze spring assures good contact. Mounts in 5/16" hole in panel up to 3/8" thick. Supplied with hex nut and fiber washer.




09-9127-1-0210 (BLK) 09-9127-1-0212 (RED)

ACCEPTS
STANDARD
BANANA PLUG




Nickel plated brass body mounts in any panel up to 3/8" thick in 5/16" hole. Supplied with hex nut, insulated washer and brass solder lug. Available in red and black.

BANANA JACK INSULATED




09-9128-1-0210 (BLK) 09-9128-1-0212 (RED)

ACCEPTS
STANDARD
BANANA PLUG




Nickel plated brass body mounts in any panel up to 3/8" thick in 5/16" hole. Supplied with hex nut, insulated washer and brass solder lug. Molded head. Available in red and black.

BANANA JACK INSULATED




09-9129-1-0210 (BLK) 09-9129-1-0212 (RED)

ACCEPTS STANDARD
BANANA PLUG



Insulated Banana Jack with wrap-around terminal. Nickel plated brass body. Molded Nylon head. Supplied with hex. nut, insulated washer and brass solder lug. Available in red and black.

BANANA JACK INSULATED




25-9235-1-03XX BANANA JACK FINISH COLOR WITH WRAPPED TERMINAL

3 AMPS CAPACITY
2500 WVDC MAX.
115°C MAX.

Closed entry receptacle .166 Dia. x .920 deep. Mounts in panels from .063 to .375 thick. Nickel plated lockwasher and 1/4-32 hex. nut.

COMPONENT	MATERIAL	FINISH
Jack body	Brass	Nickel
Sq. Wrapped pin	Phosphor bronze	Gold
Insulation	Polycarbonate	-
Nut	Brass	Nickel




25-9231-1-03XX BANANA PANEL JACK 25-9231-1-044XX INSULATED

FINISH COLOR

15 AMPS CAPACITY
2500 WVDC MAX.
115°C MAX.

Closed entry jack .166 Dia. x .920 deep. Mounts in panels from .063 to .375 thick. Nickel plated lockwasher and 1/4-32 hex. nut. Available in colors (see color chart).




COMPONENT	MATERIAL	(044) FINISH	(03) FINISH
Contact	Brass	Bright Tin	Gold
Insulation	Polycarbonate	-	-
Nut	Brass	Nickel	Nickel

25-9236-1-03XX DOUBLE BANANA JACK WITH WRAPPED WIRE TERMINAL

15 AMPS CAPACITY
2500 WVDC MAX.
115°C MAX.

Closed entry receptacle .166 Dia. x .920 deep on .750 centers. Mounts in panels from .063 to .375 thick. Nickel plated lockwasher and 1/4-32 hex. nut. One black and one red jack. Choice of black or red mounting base.




COMPONENT	MATERIAL	(03) FINISH
Sq. Wr. Term.	Brass	Gold
Insulation	Polycarbonate	-
Jack body	Brass	Nickel

25-9234-1-044XX FINISH COLOR OF MTG. BASE

5 AMPS CAPACITY
2500 WVDC MAX.
115°C MAX.

One side is a black pin jack for .080 dia. pin and the other is red banana jack .166 I.D. Mounts in panel .063 to .375 thick. Nickel plated 1/4-32 hex nut and lockwasher included. Available with black or red mounting base.




COMPONENTS	MATERIAL	FINISH
Jack body	Brass	Bright-Tin
Pin-Jack contact	Beryllium Copper	Gold
Insulation	Polycarbonate	-
Hex nut	Brass	Nickel
Lockwasher	Phosphor Bronze	Nickel

25-9233-1-044XX FINISH COLOR OF MTG. BASE

15 AMPS CAPACITY
2500 WVDC MAX.
115°C MAX.

Closed entry receptacle .166 Dia. x .920 deep on .750 centers. Mounts in panels from .063 to .375 thick. Nickel plated lockwasher and 1/4-32 hex. nut. Model has one black and one red jack. Available with black or red mounting base.



COMPONENT	MATERIAL	(044) FINISH
Contact	Brass	Bright Tin
Insulation	Polycarbonate	-
Nut	Brass	Nickel

CONCORD

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

BLK	BRN	RED	ORN	YEL	GRN	BLU	PUR	GRY	WHT
10	11	12	13	14	15	16	17	18	19