

202A111-25-0 Product Details



202A111-25-0

TE Internal Number: 806786-000

 **Active**

Molded Parts

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Molded Part Type = Molded Boot
- Family Name = 202A1
- Straight
- Military Application
- Connector Accessory Outside Diameter (Min-Max) = 7.90 - 16.50 mm

Documentation & Additional Information	
Product Drawings: Boot, Straight, Overexpanded (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available	Additional Information: Product Line Information Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Molded Part Type = Molded Boot Family Name = 202A1 - Angle = Straight - Adhesive Description = Adhesive Purchased Separately. - Size = 11 Mechanical Attachment: - Adhesive Pre-Coating = Without Dimensions: - Connector Accessory Outside Diameter (Min-Max) (mm [in]) = 7.90 - 16.50 [0.311 - 0.650] - Cable Diameter Range (mm [in]) = 3.80 - 11.90 [0.150 - 0.469] Body Features: - Material = Fluid Resistant Modified Elastomer Housing Features: Material Systems Code = 25	Configuration Features: - Material Code = 25 Industry Standards: - Government/Industry Qualification = No - Approved Standards = DEF Std 59-97 Issue 3 Type DE, MIS-34867, VG95343 Parts 6, 7, 8, & 9 RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process - RoHS/ELV Compliance History = Always was RoHS compliant Environmental: - Operating Temperature (°C) = -75 - +150 Operation/Application: - Application = Military Purchasing Information: - Adhesive Code = S1125 Other: - Brand = Raychem - Comment = Contact Raychem for additional adhesive and/or cut off boot length information