


DC0038/01/PC99-0.06

Die Cut PCM Relay Pad



Features

Low thermal resistance
Natural tack

Applications

Relay Pad

Properties

- REACH Compliant
- RoHS Compliant

Property	PC99	Unit	Tolerance	Test Method
Colour	Yellow	-	-	Visual
Thickness	0.06	mm	-	ASTM D374
Phase Change Softening Point	52	°C	-	-
Specific Gravity	2.35	g/cm ³	±0.2	ASTM D792
Working Temperature	-40 to 200	°C	-	-
Surface Resistance	>10 ¹²	Ohm-cm	-	ASTM D257
Elongation	5	%	±13	ASTM D412
Tensile Strength	0.1	Kgf/cm ²		ASTM D412
Standard Shape	-	Sheets 320-320mm	-	-
Thermal Resistance 30psi	0.1	°C-cm ² /w	-	-

Dimensions / mm							Ordering part number
A	B	C	D	E	F	G	
55.9	16.3	48.30	8.1	4			DC0038/01 - XXX - T
57.2	44.5	47.50	22.3	4.4			DC0038/02 - XXX - T
63.50	31.8	48.3	16	5.2			DC0038/03 - XXX - T
70.1	27	60	13.5	5.6			DC0038/04 - XXX - T
80	29	68	14.5	6.4			DC0038/05 - XXX - T
80	39.9	66	20.1	6.4			DC0038/06 - XXX - T
87.9	39.1	76	20	5.2			DC0038/07 - XXX - T