


CAC Customer Layout Rev: D



LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	2/22/2007	-	JL	
P	LTR	REVISION RECORD			DATE	DIN	AP

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

Restricted To:

OWN Cable Assy Configurator		MATERIAL -	HEAT TREAT -
CHK Jeremy Duncan	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD Jeremy Duncan			
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to ST			
SCALE NTS	SIZE A2	DRAWING NO C- 1906002	SHEET 2 of 4
			REV A

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Red		ST	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1906002-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	-
4-1906002-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	-
4-1906002-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	-
4-1906002-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	-
4-1906002-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	-
4-1906002-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	-
4-1906002-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	-
5-1906002-0	49.500 - 50.500	162.40 - 166.68	0.58	-	0.58	-
5-1906002-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	-
5-1906002-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	-
5-1906002-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	-
5-1906002-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	-
5-1906002-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	-
5-1906002-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	-
5-1906002-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	-
5-1906002-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	-
5-1906002-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	-
6-1906002-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	-
6-1906002-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	-
6-1906002-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	-
6-1906002-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	-
6-1906002-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	-
6-1906002-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	-
6-1906002-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	-
6-1906002-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	-
6-1906002-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	-
6-1906002-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	-
7-1906002-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	-
7-1906002-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	-
7-1906002-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	-
7-1906002-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	-
7-1906002-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	-
7-1906002-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	-
7-1906002-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	-
7-1906002-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	-
7-1906002-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	-
7-1906002-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	-
8-1906002-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	-

	A	Rev Per EC#	RELEASE	2/22/2007	-	JL	
P	LTR	REVISION RECORD		DATE	DIN	AP	

DIMENSIONS;
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

Restricted To:

DBN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Jeremy Duncan		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Jeremy Duncan					
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to ST					
SCALE NTS	SIZE A2	DRAWING NO C- 1906002		SHEET 3 of 4	REV A

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

	A	Rev Per EC#	RELEASE	2/22/2007	-	JD			
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS: meters	
0 P.L.C.	±
1 P.L.C.	±
2 P.L.C.	±
3 P.L.C.	±
4 P.L.C.	±

TOLERANCES UNLESS OTHERWISE SPECIFIED:	±
0 P.L.C.	±
1 P.L.C.	±
2 P.L.C.	±
3 P.L.C.	±
4 P.L.C.	±

Restricted To:

DWI Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Jeremy Duncan				
APVD Jeremy Duncan				
NAME FO C/A - 2 fiber, 50/125, OFNR (Riser) jacket, LC-Duplex Secure to ST				
SCALE NTS	SIZE A2	DRAWING NO C- 1906002	SHEET 4 of 4	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[5-1499598-2](#) [1754408-6](#)