

2-Port DVI/USB KVM Switch w/ Audio and Cables

MODEL NUMBER: **B004-DUA2-K-R**



Specifications

OVERVIEW	
# Of Users	1
AC Adapter	Input: 100-240V, 50/60Hz, 0.4A Output: 5V, 2A
Port Control	Push Buttons, Hotkeys
Max CPU	2
PC/Server	DVI; USB
IP Remote Access	No
Style	Desktop
PHYSICAL	
Color	Silver
ENVIRONMENTAL	
BTUs	245.52
CONNECTIONS	
Ports	2
Included KVM Cable (Equipment Side) - Connector 1	DVI-I (Male)
Included KVM Cable (Equipment Side) - Connector 2	(x2) 3.5mm (Male)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Included KVM Cable (Equipment Side) - Connector 3	USB A (Male)
Local Console Ports - Port 1	DVI-I (Female)
Local Console Ports - Port 2	(x2) USB A (Female)
Local Console Ports - Port 3	(x2) 3.5mm (Female)
CERTIFICATIONS	
Certifications	FCC, CE, RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#)

[B004-DUA2-K-R](#)