




Dimensions: mm (in.)

SPECIFICATIONS

- Rating: 10A/250VAC
- Insulation Resistance: 500VDC 100MΩ Min.
- Dielectric Strength: 1500VAC 1 Min.
- Operating Temperature: -25°C~+85°C
- Fuse Size: ø6.4x30; ø6.35x31.8
- Tolerance: ±0.3mm unless otherwise noted
- RoHS Compliant