







SINGLE DIGIT LED DISPLAYS

Digit Size	Part No.		Chip		Absolute Maximum Ratings				Electro-optical Data(At 10mA)			Drawing No.
	Common Anode	Common Cathode	Material/Emitted Color	Peak Wave Length λ_p (nm)	$\Delta \lambda$ (nm)	Pd (mw)	If (mA)	Ifp (mA)	Vf (v)		Iv. Typ. Per.Seg. (mcd)	
									Typ.	Max.		
0.56" Single-Digit	BS-A551RD	BS-C551RD	GaAsP/Red	655	40	80	40	200	1.7	2.0	1.0	SD-31
	BS-A555RD	BS-C555RD	GaP/ Bright Red	700	90	40	15	50	2.2	2.5	1.5	
	BS-A555RE	BS-C555RE										
	BS-A552RD	BS-C552RD	GaP/ Green	568	30	80	30	150	2.2	2.5	3.0	
	BS-A553RD	BS-C553RD	GaAsP/GaP/ Yellow	585	35	80	30	150	2.1	2.5	2.0	
	BS-A554RD	BS-C554RD	GaAsP/GaP/ Hi-Eff.Red	635	45	80	30	150	2.0	2.5	3.0	
			GaAsP/GaP/ Orange									
	BS-A556RD	BS-C556RD	GaAlAs/ SH Super Red	660	20	80	30	150	1.7	2.5	7.0	
BS-A55DRD	BS-C55DRD	GaAlAs/ DH Super Red	660	20	80	30	150	1.7	2.5	8.0		
0.56" Single-Digit	BS-A551RD-B	BS-C551RD-B	GaAsP/Red	655	40	80	40	200	1.7	2.0	1.0	SD-32
	BS-A555RD-B	BS-C555RD-B	GaP/ Bright Red	700	90	40	15	50	2.2	2.5	1.5	
	BS-A555RE-B	BS-C555RE-B										
	BS-A552RD-B	BS-C552RD-B	GaP/ Green	568	30	80	30	150	2.2	2.5	3.0	
	BS-A553RD-B	BS-C553RD-B	GaAsP/GaP/ Yellow	585	35	80	30	150	2.1	2.5	2.0	
	BS-A554RD-B	BS-C554RD-B	GaAsP/GaP/ Hi-Eff.Red	635	45	80	30	150	2.0	2.5	3.0	
			GaAsP/GaP/ Orange									
	BS-A556RD-B	BS-C556RD-B	GaAlAs/ SH Super Red	660	20	80	30	150	1.7	2.5	7.0	
BS-A55DRD-B	BS-C55DRD-B	GaAlAs/ DH Super Red	660	20	80	30	150	1.7	2.5	8.0		
0.60" Single-Digit	BS-A601RD	BS-C601RD	GaAsP/Red	655	40	80	40	200	1.7	2.0	1.2	SD-33
	BS-A605RD	BS-C605RD	GaP/ Bright Red	700	90	40	15	50	2.2	2.5	1.5	
	BS-A605RE	BS-C605RE										
	BS-A602RD	BS-C602RD	GaP/ Green	568	30	80	30	150	2.2	2.5	3.0	
	BS-A603RD	BS-C603RD	GaAsP/GaP/ Yellow	585	35	80	30	150	2.1	2.5	2.5	
	BS-A604RD	BS-C604RD	GaAsP/GaP/ Hi-Eff.Red	635	45	80	30	150	2.0	2.5	3.0	
			GaAsP/GaP/ Orange									
	BS-A606RD	BS-C606RD	GaAlAs/ SH Super Red	660	20	80	30	150	1.7	2.5	7.0	
BS-A60DRD	BS-C60DRD	GaAlAs/ DH Super Red	660	20	80	30	150	1.7	2.5	8.5		
0.80" Single-Digit	BS-A811RD	BS-C811RD	GaAsP/Red	655	40	80	40	200	1.7	2.0	1.3	SD-34
	BS-A815RD	BS-C815RD	GaP/ Bright Red	700	90	40	15	50	2.2	2.5	1.6	
	BS-A815RE	BS-C815RE										
	BS-A812RD	BS-C812RD	GaP/ Green	568	30	80	30	150	2.2	2.5	3.2	
	BS-A813RD	BS-C813RD	GaAsP/GaP/ Yellow	585	35	80	30	150	2.1	2.5	2.2	
	BS-A814RD	BS-C814RD	GaAsP/GaP/ Hi-Eff.Red	635	45	80	30	150	2.0	2.5	3.2	
			GaAsP/GaP/ Orange									
BS-A816RD	BS-C816RD	GaAlAs/ SH Super Red	660	20	80	30	150	1.7	2.5	7.5		
0.80" Overflow Single-Digit		BF-U811RD	GaAsP/Red	655	40	80	40	200	1.7	2.0	1.3	SD-35
		BF-U815RD	GaP/ Bright Red	700	90	40	15	50	2.2	2.5	1.6	
		BF-U815RE										
		BF-U812RD	GaP/ Green	568	30	80	30	150	2.2	2.5	3.2	
		BF-U813RD	GaAsP/GaP/ Yellow	585	35	80	30	150	2.1	2.5	2.2	
		BF-U814RD	GaAsP/GaP/ Hi-Eff.Red	635	45	80	30	150	2.0	2.5	3.2	
			GaAsP/GaP/ Orange									
		BF-U816RD	GaAlAs/ SH Super Red	660	20	80	30	150	1.7	2.5	7.5	
	BF-U81DRD	GaAlAs/ DH Super Red	660	20	80	30	150	1.7	2.5	9.0		
Alpha-Numeric Single-Digit	BS-A821RD	BS-C821RD	GaAsP/Red	655	40	80	40	200	1.7	2.0	1.3	SD-36
	BS-A825RD	BS-C825RD	GaP/ Bright Red	700	90	40	15	50	2.2	2.5	1.6	
	BS-A825RE	BS-C825RE										
	BS-A822RD	BS-C822RD	GaP/ Green	568	30	80	30	150	2.2	2.5	3.2	
	BS-A823RD	BS-C823RD	GaAsP/GaP/ Yellow	585	35	80	30	150	2.1	2.5	2.2	
	BS-A824RD	BS-C824RD	GaAsP/GaP/ Hi-Eff.Red	635	45	80	30	150	2.0	2.5	3.2	
			GaAsP/GaP/ Orange									
	BS-A826RD	BS-C826RD	GaAlAs/ SH Super Red	660	20	80	30	150	1.7	2.5	7.5	
BS-A82DRD	BS-C82DRD	GaAlAs/ DH Super Red	660	20	80	30	150	1.7	2.5	9.0		

SD-31 BS-A_C55xRD  Top view: 8.00(.315) width, 14.20(.560) height, 12.70(.500) pin pitch, PIN 1. at top left, 19.00(.748) total height, 1.2(.047) mounting tab width. Side view: 15.24(.600) height, 1.2(.047) mounting tab width. Bottom view: 8.00(.314) width, 3.00(.118)MIN. pin height, 2.54(.100) pin pitch, 3.8mm pin length. Pinout: A, B, C, D, E, F, G, DP. Pin numbers: 7, 6, 4, 2, 1, 9, 10, 5.	SD-32 BS-A_C55xRD-B  Top view: 8.00(.315) width, 14.20(.560) height, 12.50(.492) pin pitch, PIN 1. at top left, 18.00(.709) total height, 1.2(.047) mounting tab width. Side view: 15.24(.600) height, 1.2(.047) mounting tab width. Bottom view: 8.00(.314) width, 3.00(.118)MIN. pin height, 2.54(.100) pin pitch, 3.8mm pin length. Pinout: A, B, C, D, E, F, G, DP. Pin numbers: 7, 6, 4, 2, 1, 9, 10, 5.
SD-33 BS-A_C60xRD  Top view: 9.00(.355) width, 15.00(.600) height, 17.90(.705) pin pitch, PIN 1. at top left, 24.90(.980) total height, 0.80(.031) mounting tab width. Side view: 20.00(.787) height, 0.80(.031) mounting tab width. Bottom view: 8.40(.315) width, 3.00(.118)MIN. pin height, 2.54(.100) pin pitch, 5.10mm pin length. Pinout: A, B, C, D, E, F, G, RDP. Pin numbers: 7, 6, 3, 2, 1, 9, 8, 4.	SD-34 BS-A_C81xRD  Top view: 11.00(.433) width, 20.40(.80) height, 19.90(.783) pin pitch, PIN 1. at top left, 27.70(1.090) total height, 2.54(.100) mounting tab width, 0.80(.031) mounting tab width. Side view: 27.70(1.090) height, 2.54(.100) mounting tab width, 0.80(.031) mounting tab width. Bottom view: 8.40(.331) width, 3.0(.120)MIN. pin height, 2.54(.100) pin pitch, 3.5, 11, 16mm pin length. Pinout: A, B, C, D, E, F, G, RDP. Pin numbers: 6, 1, 14, 12, 10, 4, 2, 13, 9. NP: 7, 8, 15.
SD-35 BF-U81xRD  Top view: 20.40(.800) width, 27.70(1.091) height, 19.90(.783) pin pitch, PIN 1. at top left, 22.4(.094) mounting tab width, 0.90(.035) mounting tab width. Side view: 27.70(1.091) height, 2.54(.100) mounting tab width, 0.90(.035) mounting tab width. Bottom view: 8.20(.323) width, 3.00(.118)MIN. pin height, 2.54(.100) pin pitch, 15.24(.600) pin length. Pinout: A, B, C, D, E, F, G, H, J, LDP, RDP. Pin numbers: 14, 12, 13, 2, 6, 10, 16, 11, 4, 3, 5, 7. NC: 1, 8. NP: 9, 15.	SD-36 BS-A_C82xRD  Top view: 11.00(.433) width, 20.32(.800) height, 20.20(.795) pin pitch, PIN 1. at top left, 27.70(1.091) total height, 2.54x8=20.32(.80) mounting tab width, 2.2(.087) mounting tab width. Side view: 27.70(1.091) height, 2.54x8=20.32(.80) mounting tab width, 2.2(.087) mounting tab width. Bottom view: 8.50(.335) width, 3.00(.118)MIN. pin height, 2.54(.100) pin pitch, 15.24(.600) pin length. Pinout: A1, A2, B, C, D1, D2, E, F, G1, G2, J, K, L, M, N, P, DP. Pin numbers: 1, 18, 16, 13, 9, 10, 8, 4, 5, 15, 3, 2, 17, 14, 6, 7, 12.

NOTES: 1.All Dimensions are in millimeters(inches).
3.Specifications are subject to change without notice.

2.Tolerance is $\pm 0.25\text{mm}(.010")$.
4.NP:No Pin. 5.NC:No Connect.