

METER COIL RESISTANCE

Ω	ITEM			
RANGE	SD-38	SD-60	SD-80	SD-506
DC 100uA	1500 Ω	1500 Ω	1500 Ω	
DC 1mA	40 Ω	40 Ω	40 Ω	
DC 20mA	40 Ω	40 Ω		
DC 500mA	40 Ω			
DC 1A	6 Ω	6 Ω	6 Ω	
DC 3A	6 Ω			
DC 5A	6 Ω	6 Ω	6 Ω	0.01 Ω
DC 10A		6 Ω	6 Ω	0.01 Ω
DC 15A		6 Ω		0.01 Ω
DC 20A				0.01 Ω
DC 30A		6 Ω	6 Ω	
DC 50A		6 Ω	6 Ω	
DC 12V				1.3K Ω
DC 15V	40 Ω	40 Ω	40 Ω	2.3K Ω
DC 24V				3K Ω
DC 30V	40 Ω	40 Ω	40 Ω	3K Ω
DC 300V		40 Ω	40 Ω	

**P.S. ** SD-301 : 650 Ω ±10%, 500uA ±15% (STANDARD) OR
ACCORDING TO YOUR SPECIFICATION.

THREAD SIZE OF SCREWS

	SD-38	SD-60	SD-80
A	3 x 5 , P:0.5	5/32x1/4, 32W	5mm, P: 0.9
B	2.3x12, P:0.4	1/8x1/2, 40W	1/8x1/2, 40W

A : INPUT TERMINALS

B : FOUR LEGS FOR INSTALLATION