




UNIT:mm



CABLE WHITE PRINT
USB CABLE E189529  AWM 2725 28AWG/1PR AND
24AWG/2C 80℃ 30V VW-1

PIN ASSIGNMENT:



1PC/PE BAG

Electrical test:
1.100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V

CNC Tech, LLC			
Industrial Cable and Connector Technology			
⑨	PE BAG	1/1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS".
⑩	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC".
⑦	TIE	2	BLACK L=100mm
⑥	IN JACKET	3g	CLEAR LDPE(MOULD NO:NM-027)
⑤	OUT JACKET	7g	BLACK PVC-40P (MOULD NO:WM-83)
④	OUT JACKET	6g	BLACK PVC-40P (MOULD NO:WM-40)
③	CABLE	1	BLACK USB1.1 UL2725 28#/1P+24#/2C+AEB OD:4.7mm L=1800±10mm
②	CONN	1	USB A FEMALE SHELL:NICKEL PIN G/F SHORT TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB A MALE SHELL:NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR:WHITE
NO.	NAME	Q'TY	SPECIFICATION
VERSIONS/EDITION			
A/0		PROJECTION	
DRAWN		Andy	DRAWING NO
CHECKED			CUSTOMER
APPROVAL			ITEM NO.
DECIDED			DATE
			2013-08-23
			101-1010-BL-00180

CNC Tech, LLC

Industrial Cable and Connector Technology

DRAWN Andy

CHECKED

APPROVAL

DECIDED

VERSIONS/EDITION

A/0

PROJECTION

