


DIMENSIONS IN ·MM

CUSTOMER DRAWING



1. APPLICABLE CONTACT P/N :
175088-1 , 175091-1
2. APPLICABLE HSG P/N :
6-176143-6 , 6-176146-6

BLACK	85011-1
COLOR	PART NO.

GENERAL TOLERANCES	
10 MAX	± 0.2
10 OVER 30 MAX	± 0.25
30 OVER 100 MAX	± 0.3
ANGLES	$\pm 3^\circ$

O			RELEASED			JK	CS	8/6	
LTR			REVISION RECORD			DR	CHK	DATE	

© 19 AMP MFG KOREA
ALL RIGHT RESERVED AMP PRODUCTS COVERED BY PATENTS
AND OR PATENTS PENDING

AMP * AMP MFG KOREA

WIRE RANGE (AVXF WIRE) 2.0 - 3.0 mm ²		INSULATION DIA 3.1 - 3.8 mm		NAME RUBBER PLUG FOR 187 SEALED CONNECTOR				
MATERIAL NBR		FINISH/COLOR SEE TABLE		TOLERANCES 0 < XX < 10 ± 0.2 10 ≤ XX < 30 ± 0.25 30 ≤ XX < 100 ± 0.3 ANGLES ± 3°		SIZE A3	LOC DS	NO 85011
DR JK SONG	APP CS LEE			SCALE 15/1		REY 0	SHEET 1/1	
CHK CS LEE	REL CH HAN							

AMP-ME-002 (REV 9/92)

DO NOT SCALE PRINT

PRINT DIST.