

Distributed by:


JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 103924


Dimensions in mm




MFG-PA



MFG-PR



MFG-P



Rated Current	Breaking capacity	Rated Voltage	MFG52/P-PA-PR		
			UL	CS	NET
100mA	@125V/AC 10KA @250V/AC 35A	125V/250V	○	○	
125mA		125V/250V	○	○	
160mA		125V/250V	○	○	
200mA		125V/250V	○	○	
250mA		125V/250V	○	○	
300mA		125V/250V	○	○	
315mA		125V/250V	○	○	
400mA		125V/250V	○	○	
500mA		125V/250V	○	○	
600mA		125V/250V	○	○	
630mA		125V/250V	○	○	
700mA		125V/250V	○	○	
800mA		125V/250V	○	○	
1A		125V/250V	○	○	○
1.25A		125V/250V	○	○	○
1.5A		125V/250V	○	○	○
1.6A	@125V/AC 10KA @250V/AC 100A	125V/250V	○	○	○
2A		125V/250V	○	○	○
2.5A		125V/250V	○	○	○
3A		125V/250V	○	○	○
3.15A		125V/250V	○	○	○
3.5A		125V/250V	○	○	○
4A	@125V/AC 10KA @250V/AC 200A	125V/250V	○	○	○
5A		125V/250V	○	○	○
6A		125V/250V	○	○	○
6.3A		125V/250V	○	○	○
7A		125V/250V	○	○	○
8A		125V/250V	○	○	○
* 10A	@32V/AC 1000A	125V/250V	○	○	○
12A		32V			
13A		32V			
15A		32V			
16A		32V			
20A		32V			
25A		32V			
30A		32V			

Test Specification according to Standard UL 248-1,14

Electrical Characteristic

* PS:10A   Approvals only 125V

DCC. NO.	Rated Current	1.0 In	1.35 In	2 In
	In	Min.	Max.	Max.
A4 DRAWING NO.	100mA-30A	4 h	3600 S	120 S

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
JAMECO NO.		103924		GOLDSUN NO.	
DRWN: Kiki Chen				AA05062101	
VERIFY PEOPLE: Ada Zheng , Ivy Lan		Description		Rev.	
		FUSE FAST		1	
UNIT: mm		SCALE:		SHEET 1 OF 1	
				CAS No: ERN No:	