

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640032](#)
Status: **Active**
Description: Perma-Seal™ Ring Tongue Terminal for 14-16 AWG Wire, Stud 6

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)

General	
Product Family	Ring and Spade Terminals
Series	19164
Mil-Spec	N/A
Product Name	Perma-Seal™
Type	Ring
Physical	
Barrel Type	Closed
Flammability	94V-2
Insulation	NiAc™
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min: Mating (µin)	100
Plating min: Mating (µm)	2.5
Plating min: Termination (µin)	100
Plating min: Termination (µm)	2.5
Stud Size	6 (M3.5)
Wire Insulation Diameter	5.97mm (.235")
Wire Size AWG	14, 16
Wire Size mm²	1.23 - 1.94
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	SB-237-06



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19164Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool, UL Approved	0640017400
Power Crimp Tool Head for Prema-Seal™ Terminals	0640057400
10-22 AWG	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION