




安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受 控 文 件

2013 年 2 月 25 日



- 注 (NOTES):
- 材料 Material.
绝缘体:热塑性塑料,UL 94V-0;
Insert: thermoplastic,UL 94V-0;
颜色:ATP06-4S=灰色,ATP06-4S-BLK=黑色
Color:ATP06-4S=Gray,ATP06-4S-BLK=Black
 - 工作温度 Operation temperature: -55° C ~+125° C;
 - 性能参数 Specification:
 - 额定电压 Rating Voltage: 250VAC MAX;
 - 额定电流 Rating current: 25A;
 - 耐压 Withstanding voltage: 1500VAC;
 - 绝缘电阻 Insulation resistance: 1000MΩ;
 - 接触电阻 Contact resistance: 10mΩ;
 - 防水等级 Waterproof: IP67;
 - 机械寿命 Mating cycles: 100 cycles;
 - 匹配产品:ATP04-4P-XXXX (XXXX=所有扩展料号);
Mating part:ATP04-4P-XXXX (XXXX=A11 Extended Part);
 - 与产品匹配的端子和线缆规格 Mating contacts and wire.

CONTACT SIZE	MIN.INSUL O.D	MAX.INSUL O.D	WIRE RANGE
12	3.35	4.20	10~14AWG

REV ZONE				ECO				DESCRIPTION				DATE				BY				APPR			
A1				--				RELEASE NUMBER				02/09/12				--				--			
A2				--				CHANGE NOTES				19/02/13				JARRY				--			

ITEM	PART NUMBER	Qty	DESCRIPTION	REMARK
MATERIALS LIST				
UNLESS OTHERWISE SPECIFIED: 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08		MATERIAL SPECIFICATIONS:		
SIGNATURE JARRY		PROCESS SPECIFICATIONS:		
DATE 19/02/13		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OR INTERESTS ARE RESERVED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		
DRAWN Orion Li		DWC NO: ATP06-4S-XXX		
CHECKED Orion Li		THIRD ANGLE PROJECTION		
ENGINEER		FSCM NO. SIZE MASS REV. SCALE		
APPROVAL Terry Jarry		A3 A2 XX		
CUSTOMER		NEXT ASSY:		

SINE Systems Corporation
A Subsidiary of Amphenol Corporation
Assembly Connector Plug, 4 way

文件编号	幅面	质量	版次	比例
FSCM NO.	SIZE	MASS	REV.	SCALE
	A3		A2	XX
SHEET 1 OF 1	NEXT ASSY:			