


987-463

**MOULDED
BOXES
19mm**

SURFACE



2160 WHI ⁽¹⁰⁾
For surface mounting
1, 2 and 3 gang Logic
plateswitches

2161 WHI ⁽¹⁰⁾
For surface mounting
4 and 6 gang Logic
plateswitches

Brass earth terminal fitted
in base of boxes.
Knockouts provided in
sides and bases.

Dimensions:
2160 87 x 87 x 19mm;
2161 87 x 148 x 19mm


Fixing Centres:

2160 60.3mm;
2161 120.6mm

BS.5733: 1979

**MOULDED
BOXES
32mm**

SURFACE



2140 WHI ⁽¹⁰⁾
For surface mounting
1 gang Logic power
accessories

2142 WHI ⁽⁵⁾
For surface mounting
2 gang Logic power
accessories

Knockouts are provided in
base and sides for cable
entry. Box 2142 WHI has two
slots in base with 60.3mm
fixing centres for fitting over
BS. 4662 flush steel boxes


Dimensions:
1 gang 87 x 87mm;
2 gang 87 x 148mm

Fixing Centres:
1 gang 60.3mm;
2 gang 120.6mm

BS.5733: 1979

**MOULDED
BOX
44mm**

SURFACE



2031 WHI ⁽¹⁰⁾
For surface mounting
1 gang Logic power
accessories

2172 WHI ⁽⁵⁾
For surface mounting
Logic 45 amp DP
switches and Shaver

Knockouts in base and
sides for cable entry.

2172 Brass earth terminal in
base of box.
Cable clamp must be
removed when used with
Shaver Supply units


Dimensions:
2031 87 x 87 x 44mm
2172 148 x 87 x 44mm

Fixing Centres:
2031 60.3mm
2172 120.6mm

BS.5733: 1979

**MOULDED
MI CABLE BOXES
37mm**

SURFACE



2131 WHI ⁽⁵⁾
1 gang. 10 clamps

2132 WHI ⁽⁵⁾
2 gang. 12 clamps

Clamps accept 20mm
sealing pots.


2131 is not suitable for
use with 3 gang Logic or
Albany Plateswitch.

Dimensions:
2131 92 x 92mm
2132 92 x 152mm
Fixing Centres:
2131 60.3mm
2132 120.6mm

BS.5733: 1979

**MOULDED
DUAL BOX
38mm**

SURFACE



2025 WHI ⁽⁵⁾
For mounting two
1 gang accessories


2026 WHI ⁽¹⁰⁾
Moulded dividing
fillet for 2025 WHI

2025 Will accept any two
flush accessories 86mm
square with 60.3mm fixing
centres. This box has two
slots in base with 60.3mm
fixing centres for fitting
over BS. flush boxes.
Knockouts provided for
universal cable entry.

Dimensions:
86 x 172 x 38mm
BS.5733: 1979

**ARCHITRAVE
MOULDED
BOXES**

SURFACE



2151 WHI ⁽¹⁰⁾
1 gang


2152 WHI ⁽⁵⁾
2 gang

Brass earth terminal fitted
in base of boxes.

Dimensions:
1 gang 87 x 33 x 17mm
2 gang 148 x 33 x 17mm

Fixing Centres:
1 gang
60.3mm;
2 gang
120.6mm

BS.4662: 1970

**STEEL BLANK
PLATES**


3390 ALM ⁽¹⁰⁾
1 gang For Surface
Boxes 899 & 829

3370 ALM ⁽¹⁰⁾
1 gang For Surface
Boxes 891 & 821

3369 ALM ⁽⁵⁾
2 gang For Surface
Boxes 892 & 822

Dimensions:
3390 81 x 81mm
3370 76 x 76mm
3369 76 x 136mm


Fixing Centres:

**METAL FRAMES
FOR PANEL
MOUNTING**

2200 ZIC ⁽¹⁰⁾
1 gang

2202 ZIC ⁽¹⁰⁾
2 gang

Fixing Centres:
1 gang 60.3mm;
2 gang 120.6mm


**MOUNTING
FRAMES FOR
TRUNKING
18mm**

2134 WHI ⁽¹⁰⁾
1 gang

2133 WHI ⁽¹⁰⁾
2 gang

The frames are
18mm deep

Fixing Centres:
1 gang 60.3mm
2 gang 120.6mm

**GUARDIAN
SOCKET COVER**

GWR/1 ⁽¹⁾
1 gang

Helps to protect standard
sockets and switches from
the weather.
Accessories not supplied
with unit


Fixing Centres:
60.3mm

ACCESSORIES

3714 ⁽¹⁰⁰⁾
Brass Earth Terminals

3715 ⁽¹⁰⁰⁾
Brass Earth Terminals

3710 ZIC ⁽¹⁰⁰⁾
Extension Stud. M3.5
Zinc-plated steel.
Overall length 34mm



800 ZIC ⁽²⁰⁾
Box Fixing Flange

3840 ZIC ⁽¹⁰⁾
Conversion Bracket
complete with earth
terminal.

Use two **800** flanges to
mount any flush MK box
to a dry-partition wall.

3840 ZIC Converts 60mm
deep flush switch box
with 42mm fixing centre
to accommodate