

JX-55

REPLACES

PR-2863

M

ISSUE	X	DRAWING NUMBER
		3

REVISIONS

APR-2863
SRH
15 SEP 72B 0015428
SPK
14SEP05

RELEASE NO.

14SEP05

RJ

CHECK

GCH

28 MAY 69

CHECK

LSD

28 MAY 69


CHECK

LSD

28 MAY 69

CHECK

DRAWN

CORROSION RESISTANT STEEL
ACTUATOR AND BRACKET (TYPE 302).19 X .09 WIDE CORROSION
RESISTANT STEEL ROLLER
(TYPE 303)DOTTED LINES INDICATE
BASIC SWITCH IN PLACE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH ISXI-T BASIC SWITCH INSTALLED

OPERATING FORCE --- 1.5 OZ MAX

RELEASE FORCE --- 4 GRAM MIN

DIFFERENTIAL TRAVEL --- .030 MAX

OVERTRAVEL --- .020 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE 2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE

NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm .005$

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[JX-55](#)