

## Terminal Type 4

RoHS



| Part Number<br>Teilenummer                                                 | Description<br>Beschreibung | Wire Diam.<br>Drahtdurchmesser                                         | Material                                |
|----------------------------------------------------------------------------|-----------------------------|------------------------------------------------------------------------|-----------------------------------------|
| 913-073 (Reeled/auf Spule per 2000 pcs)<br>0913073001 (Single per 250 pcs) | Female / Weiblich           | 3.0-6.0 mm <sup>2</sup> /10-12AWG<br>3.0-6.0 mm <sup>2</sup> /10-12AWG | Tin plated Brass /<br>Messing, verzinkt |
| 913-074 (Reeled/auf Spule per 1000 pcs)<br>0913074001 (Single per 250 pcs) | Female / Weiblich           | 6.0-10.0 mm <sup>2</sup> /8-10AWG<br>6.0-10.0 mm <sup>2</sup> /8-10AWG | Tin plated Brass /<br>Messing, verzinkt |

## Terminal Type 5

RoHS



| Part Number<br>Teilenummer                                                 | Description<br>Beschreibung | Wire Diam.<br>Drahtdurchmesser                                             | Material                                                |
|----------------------------------------------------------------------------|-----------------------------|----------------------------------------------------------------------------|---------------------------------------------------------|
| 913-067 (Reeled/auf Spule per 3500 pcs)<br>0913067001 (Single per 250 pcs) | Female / Weiblich           | 0.82-1.33 mm <sup>2</sup> /16-18AWG<br>0.82-1.33 mm <sup>2</sup> /16-18AWG | Tin plated silicon bronze /<br>verzinnte Silikat-Bronze |
| 913-066 (Reeled/auf Spule per 3000 pcs)<br>0913066001 (Single per 250 pcs) | Female / Weiblich           | 2.09-3.32 mm <sup>2</sup> /12-14AWG<br>2.09-3.32 mm <sup>2</sup> /12-14AWG | Tin plated silicon bronze /<br>verzinnte Silikat-Bronze |