

2		1					
LOC	DIST	REVISIONS					
	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G1	REVISED DRAWING	01NOV2012	MZ	JC
			G2	REVISED CABLE RANGE	03JUL2013	MZ	JC
			G3	ADDED PARTS -3, -4, 1-3, 1-4 AND REVISED DRAWING	31JUL2013	KR	JC
			G4	PARTS -3,1-3, -4, AND 1-4 RELEASED FOR PRODUCTION	19FEB2015	KR	MZ

NOTES:

- 1

MATERIAL: POLYAMIDE GLASS FILLED
COLOUR NATURAL
- 2

MATERIAL: POLYAMIDE GLASS FILLED
COLOUR BLACK
- 3)

PACKAGING: SEE TE PACKAGING
SPECIFICATION 107-20294
- 4





DATE CODE
- 5

TE LOGO
- 6

TE PART NUMBER
- 7

CAVITY MOULD ID
- 8

AREA FOR AGENCY APPROVAL
LOGO



~1.6	11.10	9.50 - 10.40	3G H05VV-F	2	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	A	1-293607-4
~1.9	10.10	8.50 - 9.40	3G H05VV-F	2	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	A	1-293607-3
~1.7	10.00	9.00 - 9.90	3G H05VV-F	2	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	G	1-293607-2
~2.1	8.50	7.50 - 8.40	3G H05VV-F	2	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	G	1-293607-1
~1.6	11.10	9.50 - 10.40	3G H05VV-F	1	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	A	293607-4
~1.9	10.10	8.50 - 9.40	3G H05VV-F	1	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	A	293607-3
~1.7	10.00	9.00 - 9.90	3G H05VV-F	1	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	G	293607-2
~2.1	8.50	7.50 - 8.40	3G H05VV-F	1	PLASTIC NUT FOR CABLE RETENTION NECTOR* M-LINE	G	293607-1
NET WT (g)	DIM "D" NOM.	CABLE RANGE DIA. (min - MAX)	CABLE TYPE	MATERIAL / COLOUR	DESCRIPTION	REV.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. ZUCCA	22FEB2010	TE TE Connectivity							
DIMENSIONS: mm		CHK M. ZUCCA	22FEB2010	NAME PLASTIC RING NUT FOR CABLE RETENTION NECTOR* M-LINE							
		APVD G. TURCO	22FEB2010								
		PRODUCT SPEC 108-20304									
		APPLICATION SPEC 114-20152									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT SEE TABLE		SIZE A3	CAGE CODE 00779	DRAWING NO C-293607	RESTRICTED TO -				
MATERIAL SEE NOTE 1 AND NOTE 2		FINISH -		Customer Drawing				SCALE 3:1	SHEET 1	OF 1	REV G4