




FEATURES:

- Multi-purpose test clips allow four ways to connect to a device under test
 - U-shaped nose for blade shaped terminals
 - Notched jaw for gripping screw heads, bare wire or terminals
 - Serrated teeth for gripping threaded or wire wrapped terminals
 - Cluster of sharp needles for piercing small gauge wires (#22-28 AWG)

MATERIALS:

Jaws: Non-rusting Nickel Copper Alloy

Boot: Vinyl

Wire: 18 AWG, Silicone, 0.144" outside diameter

Banana Plug:

Spring: Beryllium Copper, nickel plated

Body: Brass Nickel Plated

Insulation: Polypropylene

RATINGS:

Operating Voltage: Hand-held 30 VAC/60 VDC

Hands free operation in a controlled voltage environment: 300 VRMS

Current: 8 Amperes

ORDERING INFORMATION: Model 6485-48-*

*=Color; 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue

Standard Length = 48" (122 cm).

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90949 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6485-48-0](#) [6485-48-2](#)