

Ratings:

Current	10A
Voltage	300 V
Wire Size	20-14AWG
Test Voltage	2.0 kV

Rated Cross Section:

Single Wire (solid)	1.5mm ²
Stranded Wire (flexible)	on request
Stranded Wire with Ferrules	on request

Dimensions:

Spacing	5.0mm
PCB Hole Diameter	1.0mm
Stripped Length	9.0mm

Materials:

Insulating Material	PA
Flammability	UL94V-0
Temperature	-30°C/+105°C
Tension Spring	Stainless Steel
Contact	Cu
Color	Slade Gray

